




Portata 15000 g/min

Mod. 4048



Portata 10000 g/min

Mod. 4049



Portata 7000 g/min

Mod. 4050



Portata 4900 g/min

Mod. 4051

ACCESSORI vedi pag. 55-63

Modello	4048	4049	4050	4051
Alimentazione	Aria Compressa Min 2 Max 8 bar (30 - 116 psi)			
Rapporto di compressione	30 : 1	50 : 1	90 : 1	75 : 1
Pressione max uscita	240 bar (3500 psi)	400 bar (5800 psi)	720 bar (10450 psi)	600 bar (8700 psi)
Portata	15000 g/min	12000 g/min	7000 g/min	4900 g/min
Frequenza max pompate/min	150	120	60	60
Connessione aria compressa	F 1/2" BSP			
Connessione uscita prodotto	M 1" BSP			
Consumo aria max a 8 bar	1,86 m ³ /min	1,92 m ³ /min	1,80 m ³ /min	1,80 m ³ /min
Diametro pistone pneumatico	100 mm	125 mm	160 mm	160 mm
Diametro pescante	50x22 mm			
Per fusti da	180 kg			
Peso	18 kg	22 kg	24 kg	25 kg

Mod. 4048

Distanza (m)	Portata grasso (kg/min)				Pressione (bar)
	NLGI 0	NLGI 1	NLGI 2	NLGI 3	
1	15,00	12,70	11,60	9,30	240
5	14,60	10,30	8,50	5,30	200
10	10,50	8,00	6,20	3,80	165
20	8,60	5,20	4,10	3,10	140
30	6,50	4,40	3,80	2,20	130
40	5,30	4,10	3,40	1,70	110
50	4,20	3,80	6,00	0,80	85
70	3,00	2,50	1,80	0,30	60

Mod. 4049


Distanza (m)	Portata grasso (kg/min)				Pressione (bar)
	NLGI 0	NLGI 1	NLGI 2	NLGI 3	
1	12,00	9,60	8,60	7,80	400
5	11,80	9,00	7,90	5,60	360
10	11,10	8,20	6,70	4,00	240
20	9,50	6,40	4,80	2,30	220
30	7,70	4,70	3,10	2,10	180
40	6,90	3,20	2,50	1,70	150
50	6,50	2,80	2,20	1,40	110
70	6,10	2,50	1,90	0,90	85

Mod. 4050

Distanza (m)	Portata grasso (kg/min)				Pressione (bar)
	NLGI 0	NLGI 1	NLGI 2	NLGI 3	
1	7,00	6,30	5,70	5,10	720
5	6,80	5,80	5,20	4,10	680
10	6,40	5,30	4,70	3,50	420
20	5,90	4,30	3,50	2,10	400
30	4,80	3,30	2,90	1,90	370
40	4,50	2,90	2,50	1,70	340
50	4,30	2,60	2,20	1,60	250
70	4,00	2,20	2,10	1,30	180

Mod. 4051

Distanza (m)	Portata grasso (kg/min)				Pressione (bar)
	NLGI 0	NLGI 1	NLGI 2	NLGI 3	
1	4,90	4,70	4,60	3,90	600
5	4,70	4,50	4,10	3,10	580
10	4,30	4,00	3,60	2,50	360
20	4,20	3,70	3,00	1,70	340
30	4,00	2,70	2,20	1,40	320
40	3,80	2,50	1,90	1,20	280
50	3,70	2,20	1,70	1,00	200
70	3,60	1,80	1,60	0,80	120



Prestazioni rilevate in laboratorio alle seguenti condizioni: Grasso al litio tipo NLGI 0 a 22°C - Pressione alimentazione aria 8 bar